



Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

AQ-3700

Features & Options

TALLER & LONGER THAN AQ-3000

Standard Features:

- Double Wall Stainless Steel Chamber
- Stainless Steel Spray Arms
- Oscillating Spray Arms
- Deck & Loading System
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Front Door Window
- Heavy-Duty Caster Wheels
- Fill & Drain Hose Set
- 1.5 HP Motor/ Stainless Steel Pump
- 115V, 50/60Hz, 20 Amp AC Operation

Optional Features:

- Disinfectant Application System
- Wheelchair Wheel Rotation System
- Utility Equipment Rack
- Utility Wash Trays
- Air Dry Blower
- Electronic Temperature Monitor
- 230V, 50/60Hz, Single Phase AC Operation
- Operations Validation System (Including Printed Performance Records)



Total Outer Dimensions

- **Width** 33-1/2"
- **Length** 72"
- **Height** 70-3/4"

Effective Chamber Dimensions

- **Width** 26-1/2"
- **Length** 58-1/2"
- **Height** 52"

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain, connect the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.