



Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

# AQ-1500

## Features & Options

### FEATURES INCLUDE **OSCILLATING SPRAY ARMS** FOR INCREASED SPRAY ACTION.

#### Standard Features:

- Double Wall Stainless Steel Chamber
- Stainless Steel Spray Arms
- Oscillating Spray Arms
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Heavy-Duty Caster Wheels
- Fill & Drain Hose Set
- 1 HP Motor/ Stainless Steel Pump
- 115 Volt, 20 Amp AC Operation

#### Optional Features:

- Disinfectant Application System
- Utility Wash Trays
- Front Door Window
- Air Dry Blower
- 1.5 HP Motor Upgrade/ Stainless Steel Pump
- 230V, 50/60Hz, Single Phase AC Operation



#### *Total Outer Dimensions*

- **Width** 33-1/2"
- **Length** 64"
- **Height** 62"

#### *Effective Chamber Dimensions*

- **Width** 26-1/2"
- **Length** 51-1/4"
- **Height** 41-1/2"

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain, connect the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.