



Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

AQ-3800

Features & Options

LARGE WASH CHAMBER WITH A SMALL FOOTPRINT

Standard Features:

- Double Wall Stainless Steel Chamber
- Stainless Steel Spray Arms
- Oscillating Spray Arms
- Deck & Loading System
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Front Door Window
- Heavy-Duty Caster Wheels
- Fill & Drain Hose Set
- 2 HP Motor/ Stainless Steel Pump
- 230V, 50/60Hz, Single Phase AC Operation

Optional Features:

- Disinfectant Application System
- Utility Wash Trays
- Electronic Temperature Monitor
- Pass Through Option (Two Doors)
- Operations Validation System (Including Printed Performance Records)



Total Outer Dimensions

- **Width** 63-1/4"
- **Length** 57-1/2"
- **Height** 73"

Effective Chamber Dimensions

- **Width** 40-1/2"
- **Length** 55"
- **Height** 48"

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain, connect the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.