



AQUA PHASE™

Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

AQ-4200

Features & Options

A “TAKE-DOWN” MODEL

SLIGHTLY NARROWER THAN THE AQ-4000

Standard Features:

- Double Wall Stainless Steel Chamber
- Stainless Steel Spray Arms
- Oscillating Spray Arms
- Ramp Set (2 @ 4-ft each)
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Front Door Window
- Heavy-Duty Caster Wheels
- Adjustable Leveling Feet
- Fill & Drain Hose Set
- 2 HP Motor/ Stainless Steel Pump
- 230V, 50/60Hz, Single Phase AC Operation



Optional Features:

- Disinfectant Application System
- Entry/Exit Doors-Pass Through Model
- Conveyor Floor Transfer System
- Utility Wash Trays
- Electronic Temperature Monitor
- Pump Motor Upgrade - 3 HP
- Extended Ramp Sets
- Operations Validation System (Including Printed Performance Records)

Total Outer Dimensions

- **Width** 59-1/4”
- **Length** 96-3/4”
- **Height** 73”

Effective Chamber Dimensions

- **Width** 36-1/2”
- **Length** 93-3/4”
- **Height** 48-1/2”

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain, connect the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.