



Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

# AQ-8000

## Features & Options

### VERTICAL BACKBOARD WASHER

ALLOWS OPERATOR TO WASH UP TO

**TWO BACKBOARDS** AT ONE TIME

#### Standard Features:

- Stainless Steel Chamber
- Stainless Steel Spray Arms
- Carousel Style Loading & Wash System
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Front Door Window
- Heavy-Duty Caster Wheels
- Adjustable Leveling Feet
- Fill & Drain Hose Set
- 115V, 50/60Hz, 20 Amp AC Operation

#### Optional Features:

- Disinfectant Application System
- Electronic Temperature Monitor
- 230V, 50/60Hz, Single Phase AC Operation
- Operations Validation System (Including Printed Performance Records)



#### Total Outer Dimensions

- Width 66-1/2"
- Length 36"
- Height 104-1/2"

#### Effective Chamber Dimensions

- Width 36-3/4"
- Length 34-1/4"
- Height 81-1/2"

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain, connect the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.