



AQUA PHASE™

Washers & Sanitizers to automatically wash and apply disinfectants to wheelchairs and other hard-to-clean medical equipment.

AQ-F270

Features & Options

Stretched Version of the AQ-F250

Taller & Longer - see below

Standard Features:

- Double Wall Stainless Steel Chamber
- PVC Spray Arms
- Variable Wash Time Cycles (3, 5, or 7 Minute)
- Wash and Rinse Cycles
- Automatic Chemical Injection
- LCD Status Display
- Heavy-Duty Caster Wheels
- Fill & Drain Hose Set
- 1 HP Motor / Stainless Steel Pump
- 115 Volt, 20 Amp AC Operation

Optional Features:

- Front Door Window



Total Outer Dimensions

| | <u>AQ-F250</u> | <u>AQ-F270</u> |
|-----------------|----------------|----------------|
| • Width | 33 1/2" | 33 1/2" |
| • Length | 64" | 72" |
| • Height | 62" | 70 3/4" |

Effective Chamber Dimensions

| | <u>AQ-F250</u> | <u>AQ-F270</u> |
|-----------------|----------------|----------------|
| • Width | 26 1/2" | 26 1/2" |
| • Length | 51 1/4" | 58 1/2" |
| • Height | 41 1/2" | 52" |

Like all Aqua Phase models, in order to operate the machine once the unit is located, all you need to do is hook up two hoses — one for the hot water fill and one for the drain. Plug the Aqua Phase to an appropriate power source and begin saving time, improving efficiency and enhancing your infection control protocol.